

TYPICAL GAIN RANGES BASED ON CONTRAST LEVEL SELECTION



Australian Opal				
Ounces of Top Coat Activator required for desired gain*				
Desired Gain	No Contrast	Light	Medium	High
0.90				2.0
0.95				3.0
1.00			2.0	4.0
1.05			3.0	5.0
1.10		2.0	4.0	6.0
1.15	2.0	3.0	5.0	7.0
1.20	3.0	4.0	6.0	8.0
1.25	4.0	5.0	7.0	
1.30	5.0	6.0	8.0	
1.35	6.0	7.0		
1.40	7.0	8.0		
1.45	8.0			
Gain levels in this range are recommended for most normal applications. Gain levels outside this range are not recommended without very careful evaluation of your requirements.				

*Some fluid will remain in the measuring cup and that is normal and considered in the above guidelines. Depending on the gain you decide to apply you may have a substantial amount of Top Coat Activator left over after mixing. Bottles are packed to allow for all gain level requirements. Many gain targets will require less than 5 oz. of the Activator. Above gain levels will be accurate within +/- 13%. Variables include exact fill amount and mixing. All applications require a minimum of 2 oz. of top coat activator. If you have a special application that requires a gain outside of the gains offered above please contact customerservice@diytheatre.com for direction. Rev 1206.